

Adapter Plate for #55-028



#55-037

#55-037

Stock **#55-037** 20+ In Stock

-

1

+

A\$60⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$60.40 each
Qty 10+	A\$54.24 each
Need More?	Request Quote

Product Downloads

General

Type:

Adapter Brackets & Plates

Physical & Mechanical Properties

1.57	Length (inches):
40.00	Length (mm):

Dimensions (mm):

40 x40 x5

Threading & Mounting

Mounting Threads:

(4) M2 x0.4, (4) M3 x0.5, (1) 1/4-20

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

View

Reach 247:


Compliant

Product Details

- Precision Micrometer Drive and Manual Drive Options
- 360° Coarse Rotation
- Micrometer Drive Models Provide ±5° Fine Rotation
- Black Anodized Aluminum Construction

Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments. Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

Technical Information



Units: mm