


[See all 9 Products in Family](#)

Adapter Plate for #55-029



#55-038



Stock **#55-038** 5 In Stock

-

1

+

A\$62^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	A\$62.00 each
Qty 10+	A\$55.68 each
Need More?	Request Quote

Product Downloads

General	
Adapter Brackets & Plates	Type:
Physical & Mechanical Properties	
2.36	Length (inches):
	Length (mm):

60.00	
60 x 60 x 7	
Dimensions (mm):	
Threading & Mounting	
Mounting Threads: (4) M4 x 0.7, (4) M3 x 0.5, (4) M2 x 0.4, (1) 1/4-20	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	

Product Details

- Precision Micrometer Drive and Manual Drive Options
- 360° Coarse Rotation
- Micrometer Drive Models Provide ±5° Fine Rotation
- Black Anodized Aluminum Construction

Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments. Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

Technical Information

