

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Allied Vision Alvium Right Angle USB 3.1 Cameras](#)

[See all 128 Products in Family](#)

Allied Vision Alvium 1800 U-120m, 1/3" 1.2MP C-Mount, Right Angle USB 3.1 Monochrome Camera

See More by [Allied Vision](#)



Stock #23-200 3-5 DAYS

[Similar Cameras](#)

- 1 + **A\$588.80**

ADD TO CART

Qty 1+

A\$588.80

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:

Monochrome Camera
Manufacturer: Allied Vision
Mounting Threads: 1/4-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium Right Angle
Model Number: 1800 U-120m
Imaging Sensor: ON Semi AR0135CS
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 1.20
Pixels (H x V): 1,280 x 960
Pixel Size, H x V (µm): 3.75 x 3.75
Sensing Area, H x V (mm): 4.8 × 3.6
Frame Rate (fps): 52.00
Pixel Depth: 12 bit
Exposure Time: 57µs - 12s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 1.30
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 38 (includes connectors and lens mount)
Weight (g): 60
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel (Right Angle)
Dynamic Range (dB): 63
Operating Temperature (°C): +5 to +65
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

