

Allied Vision Alvium G1-234c, 1/1.2" 2.4MP C-Mount, GigE PoE Color Camera

See More by [Allied Vision](#)



+1

Stock **#23-542** 3-5 DAYS

[Similar Cameras](#)

− 1 +

A\$1,092.80

ADD TO CART

Qty 1+

A\$1,092.80

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer:

Allied Vision
Mounting Threads: ¼"-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 32MB
Camera Family: Alvium G1
Model Number: Alvium G1-234c
Imaging Sensor: Sony IMX249
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.2"
Resolution (MegaPixels): 2.35
Pixels (H x V): 1,936 x 1,216
Pixel Size, H x V (µm): 5.86 x 5.86
Sensing Area, H x V (mm): 11.3 x 7.1
Frame Rate (fps): 40.00
Pixel Depth: 10/12 Bit
Exposure Time: 53µs - 10s
Connector: GigE, RJ45 with Screw Locks
Power Supply: PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581
Power Consumption (W): External power: 3.0 W at 12 VDC Power over Ethernet: 3.3 W
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 41 x 29 x 29
Weight (g): 65
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): -20 to +50
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 10-pin TFM
Machine Vision Standard: GigE Vision V1.2, GenICam V2.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

