

Basic Liquid Crystal Controller



Stock **#63-045** CLEARANCE 3-5 DAYS

- 1 + **A\$1,119.92**

ADD TO CART

Qty 1+
A\$1,119.92

Volume Pricing
Request Quote

Get Product Downloads

Dimensions (inches):
7.0 x 5.0 x 3.1

Weight (lbs):
2.00

Power Requirement:
115/230 V, 50/60 Hz, 5 W

Output Voltage (V):
2kHz AC square λ adjustable 0-25V RMS; 50% duty cycle, minimal DC bias

Voltage Resolution:
3mV

Modulation:
Internal: 0.7-150Hz
TTL input: 12V maximum DC-1 kHz

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)

