

Basler ace acA1920-150um Monochrome USB 3.0 Camera



Stock **#36-739** 3-5 DAYS

- 1 + **A\$1,086.40**

ADD TO CART

Qty 1+
A\$1,086.40

Volume Pricing
Request Quote

Get Product Downloads

Video Output: USB 3.0
Type: Monochrome Camera
Manufacturer: Basler
Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-517

Image Buffer: Not Specified
Camera Family: ace
Model Number: acA1920-150um
Imaging Sensor: ON Semi PYTHON 2000
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 2.30
Pixels (H x V): 1,920 x 1,200
Pixel Size, H x V (µm): 4.8 x 4.8
Sensing Area, H x V (mm): 9.22 x 5.76
Frame Rate (fps): 150.00
Pixel Depth: 10 bit
Exposure Time: Programmable via camera API, hardware trigger
Connector: USB 3.0, Micro-B with Screw Locks
Power Supply: Power over USB
Power Consumption (W): 3
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 29.3 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 80
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 56.9
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant