

[See all 59 Products in Family](#)

Basler ace acA2440-35um Monochrome USB 3.0 Camera

See More by [Basler](#)



Basler ace USB 3.0 Cameras (Front)



Stock **#35-925** **2 In Stock**

[Similar Cameras](#)

-

1

+

A\$1,408⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,408.00 each
Need More?	Request Quote

Product Downloads

Monochrome		Spectrum:
General		
Monochrome Camera		Type:
acA2440-35um		Model Number:

Basler	Manufacturer:
ace	Camera Series:
Physical & Mechanical Properties	
29.3 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
80	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
2/3"	Sensor Format:
5.00	Resolution (Megapixels):
35.00	Frame Rate (fps):
2,448 x 2,048	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
8.45 x 7.07	Sensing Area, H x V (mm):
Sony IMX264	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10/12 bit	Pixel Depth:
Programmable via camera API, hardware trigger	Exposure Time:
73.4	Dynamic Range (dB):
USB3 Vision v1.0	Machine Vision Standard:
Electrical	
2.5	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.0	Interface:
USB 3.0, Micro-B with Screw Locks	Connector:
Power over USB	Power Supply:
1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #88-517	Mounting Threads:
Environmental & Durability Factors	
0 to +50	Operating Temperature (°C):
-20 to +80	Storage Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:


Compliant	Reach 235:
---------------------------	------------

Product Details

- High Speed USB 3.0 Interface
- Ultra-Small Form Factor
- Fully USB3 Vision Compliant

Basler ace USB 3.0 Cameras are an ideal choice for analog camera users looking to upgrade to digital, or for FireWire or USB 2.0 users looking for faster data transfer rates. Basler ace USB 3.0 Cameras are fully USB3 Vision compliant and feature a small, 29 x 29mm form factor that makes them easy drop-in replacements for many analog, FireWire, or USB 2.0 cameras. Additionally, these USB 3.0 cameras feature screw-locking USB 3.0 ports for increased ruggedness in demanding applications, such as factory floor use. All cameras include the Basler Pylon SDK software and driver.

Technical Information



MT9P031 Sensor QE Curve