

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [FLIR Blackfly® S PoE GigE Cameras](#)


[See all 51 Products in Family](#)

BFS-PGE-63S4C-C PoE GigE Blackfly® S, Color Camera

See More by [FLIR](#)



FLIR® Blackfly® S PoE GigE Cameras



Stock **#12-756** 3-5 DAYS

[Similar Cameras](#)

− 1 +

A\$662.40

ADD TO CART

Qty 1+

A\$662.40

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer: FLIR
Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-210
Image Buffer: 240MB
Camera Family: Blackfly® S
Model Number: BFS-PGE-63S4C-C
Imaging Sensor: Sony IMX178
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 6.30
Pixels (H x V): 3,072 x 2,048
Pixel Size, H x V (µm): 2.4 x 2.4
Sensing Area, H x V (mm): 7.37 x 4.92
Frame Rate (fps): 19.00
Pixel Depth: 8/12/16/24 bit
Exposure Time: 25µs - 30s
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately: USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: Not Available
Power Consumption (W): <2.5
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 30 (excludes connectors and lens mount)
Weight (g): 36
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 73.35
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance:

