

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [FLIR Blackfly® S USB 3.1 Cameras](#)

[See all 70 Products in Family](#)

BFS-U3-50S4C-C, USB 3.1 Blackfly® S, Color Camera

See More by [FLIR](#)



FLIR Blackfly® S USB3 Camera (front)



Stock **#22-765** 3-5 DAYS

[Similar Cameras](#)

- 1 +

A\$1,484.80

ADD TO CART

Qty 1+
A\$1,484.80
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:
Color Camera

Manufacturer: FLIR
Mounting Threads: 1/4-20 with Tripod Mount Adapter #15-838
Image Buffer: 240MB
Camera Family: Blackfly® S
Model Number: BFS-U3-50S4C-C
Imaging Sensor: Sony IMX547
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,448 x 2,048
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 6.71 x 5.61
Frame Rate (fps): 72.00
Pixel Depth: 8/10/12 bit
Exposure Time: Not Specified
Connector: USB 3.1 Gen 1, Micro-B with Screw Locks
Power Supply: Power over USB or via GPIO with #88-063
Power Consumption (W): Not Specified
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 39 (excludes connectors and lens mount)
Weight (g): 53
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 64.81
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: USB3 Vision v1.0

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

