

Blue M35.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-571 3-5 DAYS

-

1

+

A\$232.00

ADD TO CART

Qty 1-9

A\$232.00

Qty 10+

A\$221.28

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-400, 550-1210

Clear Aperture CA (mm):
30.50

Coating:
Hard Coated

Filter Thread:

M35.5 x 0.50
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 37.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View