

Blue M58 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-724 3-5 DAYS

-

1

+

A\$345.60

ADD TO CART

Qty 1-9

A\$345.60

Qty 10+

A\$329.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-400, 550-1219

Clear Aperture CA (mm):
53.00

Coating:
Hard Coated

Filter Thread:

M58 x 0.75
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 60.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View