

TECHSPEC[®] C-Mount Achromat Pair 1:1 with 30 and 30mm Focal Lengths



Stock #87-185 3-5 DAYS

-

1

+

A\$592.00

ADD TO CART

Qty 1-5
A\$592.00
Qty 6+
A\$473.60
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
40-20

Working f#:
f/1.4 - f/37

Coating:
VIS 0° (425-675nm)

Coating Specification:
R_{avg} ≤0.4% @ 425 - 675nm

Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 30.0
Effective Focal Length EFL B (mm): 30.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:1
Object Distance (mm): 15.00
Image Distance (mm): 13.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View