

Coarse Movement, 1/4-20, Rack & Pinion



Rack and Pinion Movement

Stock #54-793 3-5 DAYS



1



A\$676.80

ADD TO CART

Qty 1+

A\$676.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):

Rack and Pinion Block: 50 H x30 Wx50 L

Travel (mm):

35 (+23/-12) in Y

Type:

Rack and Pinion Mount

Travel Per Knob Rotation (mm):

25.5

Load Capacity (kg):

2.00

Note: 1/4-20 Stud
Type of Movement: Linear (Y)
Type of Adjustment: Coarse Movement
Optical Centerline from Post (mm): 51.00
Mounting Post Hole and Thread: 3/4" Diameter Post 1/4-20 Tapped Hole

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View