

Coarse Movement, 50mm Dia Thru w/ Rotation, Rack & Pinion



#59-320

Stock **#59-320** CLEARANCE 3-5 DAYS

⊖ 1 ⊕

A\$279.92

ADD TO CART

Qty 1+

A\$279.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
Rack and Pinion Block: 50.8 H x28.6 W x50.8 L

Travel (mm):
35 (+23/-12) in Y

Type:
Rack and Pinion Mount

Weight (lbs):
1.31

Travel Per Knob Rotation (mm):
25.5

Load Capacity (kg): 2.00
Note: 50 mm Diameter Thru-Hole
Type of Movement: Linear (Y), Rotation
Type of Adjustment: Coarse Movement
Optical Centerline from Post (mm): 100.00
Mounting Post Hole and Thread: ¾" Diameter Post ¼-20 Tapped Hole

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View