

Coarse Movement, 65mm Diameter Thru Hole, Rack & Pinion



65mm Diameter Thru Hole

Stock **#39-357** 3-5 DAYS

⊖ 1 ⊕

A\$694.40

ADD TO CART

Qty 1+

A\$694.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
Rack and Pinion Block: 63.5 H x31.75 Wx63.5 L

Travel (mm):
57.15 in Y

Type:
Rack and Pinion Mount

Weight (lbs):
1.5

Travel Per Knob Rotation (mm):
25.5

Load Capacity (kg): 2.00
Note: 65 mm Diameter Thru-Hole
Type of Movement: Linear (Y)
Type of Adjustment: Coarse Movement
Optical Centerline from Post (mm): 110.00
Mounting Post Hole and Thread: ¾" Diameter Post 5/16-18 Tapped Hole

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View