

Coherent® EnergyMax 1110746 | 500μJ-1000mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-386** [CONTACT US](#)

-

1

+

A\$2,816.00

ADD TO CART

Qty 1+

A\$2,816.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Active Area Diameter (mm):
25

Connector:
DB25

Model Number:
J-25MB-HE
Coherent Part Number: 1110746

Type:
[Meter required](#)

Type of Sensor: Pyroelectric
Length of Cable (m): 2.5
Linearity (%): ±3
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 1064
Noise Equivalent Energy (μJ): <16
Maximum Repetition Rate (pps): 1000
Maximum Incident Beam Power (W): 5
Maximum Pulse Width (μs): 17
Compatible Meters: #35-203 or #66-277
Wavelength Range (nm): 190 - 12000
Maximum Incident Energy Density: 500mJ/cm ² (10ns, 1064nm)
Energy Range: 500μJ - 1J
Preferred Meter: #88-412

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View