

Coherent® PowerMax Pro 150 HD Measurement System 1266709 | 170W

See More by [Coherent®](#)



Coherent USB-PowerMax Pro Fast Measurement Systems

Stock **#12-413** [CONTACT US](#)

-

1

+

A\$4,536.00

ADD TO CART

Qty 1+
A\$4,536.00

Volume Pricing
Request Quote

Get Product Downloads

Model Number:
1266709

Type:
[Meter required](#)

Length of Cable (m):
2.5

Active Area (mm):
30 x30

Computer Interface:

DB25
Rise Time (μs): ≤10
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 810
Spectral Compensation Accuracy (%): ±3
Cooling Method: Water/Air (intermittent)
Maximum Incident Power Density (kW/cm²): 14
Fall Time (μs): ≤10
Compatible Meters: #35-203
Wavelength Range (nm): 400 - 1100, 9000 - 11000
Power Range (Water-Cooled): 100mW to 150W
Maximum Incident Energy Density: 33mJ/cm² (10ns; 1064nm)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View