


## Concentric Square Target



#46-248

Stock **#46-248** **4 In Stock**

⊖ 1 ⊕ **A\$1,072<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-4	<b>A\$1,072.00</b> each
Qty 5+	<b>A\$1,019.84</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

**Pattern Size (mm):**  
1, 2, 3, 4, 5, 10, 15, 20, 30, 40, 50

**Dimensions (mm):**  
76.2 x 76.2

**Thickness (mm):**  
1.50

**Line Width Tolerance (mm):**  
±0.001

## Optical Properties

**Coating:**

Vacuum Deposited Chromium Oxide (specular reflectivity <5% @ 550nm)

**Substrate:** □

Float Glass

**Surface Quality:**

20-10

**Surface Flatness (P-V):**

λmm

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 240:**

[Compliant](#)

## Product Details

- For Calibration of Measurement Software
- NIST Traceable Certificate of Accuracy Included
- 1mm to 50mm Squares

Concentric Square Targets provide an accurate means of calibrating measurement software for image processing. The squares vary in dimensions to accommodate different fields of view. The square targets are NIST Traceable Certificate of Accuracy included. Concentric Square Targets are offered in 1 to 50mm pattern sizes. Included in the packaging is a serialized NIST Traceable Certificate of Accuracy per ML-STD-45662A.