

Cyan M25.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-742 3-5 DAYS



1



A\$198.40

ADD TO CART

Qty 1-9

A\$198.40

Qty 10+

A\$188.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-450, 600-1020

Clear Aperture CA (mm):
21.00

Coating:
Hard Coated

Filter Thread:

M25.5 x 0.50
Color: Cyan
Center Wavelength CWL (nm): 505.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 90.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 27.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View