

Preloaded Norland Optical Adhesive NOA 88 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock #14-840 3-5 DAYS

- 1 + **A\$60.80**

ADD TO CART

Qty 1-4

A\$60.80

Qty 5+

A\$57.12

Volume Pricing

[Request Quote](#)

Get Product Downloads

Size (oz):
0.34

Glass Bonding:
Excellent

Metal Bonding:
Excellent

Plastic Bonding: Fair
Viscosity (cps): 250
Durability: Hard & Flexible
Index of Refraction n_d: 1.56 @ 589nm
Norland Number: 88
Shelf Life: 4 months
Type: Barrel
Typical Applications: Low outgassing and low viscosity for bonding glass or metal. Excellent transmission in the UV.
Note: Contains 10g of adhesive
Absorption Range (nm): 315 - 395
Bonding Type: Glass to Glass/Metal
Energy for Full Cure (J/cm²): 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant