

DL-UV Doubler Tube for 2X Magnification

See More by [Infinity Photo-Optical Company](#)



Stock **#58-947** **8 In Stock**

-

1

+

A\$1,088^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,088.00 each
Need More?	Request Quote

Product Downloads

General

Type:	
Lens Accessory	

Regulatory Compliance

RoHS 2015:	
Compliant	
Reach 224:	

Product Details

- Available in Standard and Right Angle Versions
- Magnification Range from 0X to 8.0X
- Max. 2/3" Sensor Format
- Direct Video C-Mount Coupling
- No Adapters Required

The InfiniProbe™ is available in a model designed to continuously focus UV light. The InfiniProbe™ 8.0X UV Video Microscope boasts a magnification range of 0-8X, supports up to a 2/3" format sensor, and offers direct video C-Mount coupling while incorporating exceptional resolution in the UV spectrum. Focusing from infinity down to a 0.8mm FOV at a WD of 20mm, the InfiniProbe™ 8.0X UV is capable of yielding magnifications up to 328X on a 13 inch monitor (based on a 1/2" sensor). To double magnification, add the DL-UV ([#58-947](#)) or LDL-UV ([#58-948](#)) Doubler Tube on the C-Mount. Mounting is provided through an included 1/4-20 mounting clamp. A variety of UV lighting options are available including the [MH-100 illuminator](#), [UV curing lamps](#), and [Broadband Fiber Coupled Illuminators](#).

Technical Information

