

TECHSPEC® 30mm Sq, 5kg Load Capacity, 8mm Travel, English Dovetail Stage



#16-711: Dovetail Stage, 30mm SQ, English



Stock **#16-711** 3-5 DAYS

- 1 +

A\$176.00

ADD TO CART

Qty 1-9
A\$176.00
Qty 10+
A\$155.20
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive:

Lead Screw
Drive Orientation: Center Drive
Type: English
Stage Size (mm): 30 x 30
Travel (mm): 8
Travel (inches): 0.31
Construction: Matte Black Finish Brass
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 5
Mounting Threads: (1) 1/4-20, (8) 2-56
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 10
Included Hardware: 4X 2-56, 5/16"L Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View