

**TECHSPEC® 65mm Sq, 15kg Load Capacity, 25mm Travel, English Dovetail Stage**



#16-713: Dovetail Stage, 65mm SQ, English



Stock **#16-713** 3-5 DAYS

- 1 +

**A\$288.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$288.00                     |
| Qty 10+                       |
| A\$253.60                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Dovetail

Type of Drive:

|                                                                                                                   |
|-------------------------------------------------------------------------------------------------------------------|
| Lead Screw                                                                                                        |
| <b>Drive Orientation:</b><br>Center Drive                                                                         |
| <b>Type:</b><br>English                                                                                           |
| <b>Stage Size (mm):</b><br>65 x 65                                                                                |
| <b>Travel (mm):</b><br>25                                                                                         |
| <b>Travel (inches):</b><br>0.98                                                                                   |
| <b>Construction:</b><br>Matte Black Finish Brass                                                                  |
| <b>Leadscrew Pitch (mm):</b><br>0.5                                                                               |
| <b>Load Capacity (kg):</b><br>15                                                                                  |
| <b>Mounting Threads:</b><br>(9) 1/4-20, (4) 6-32, (8) 2-56                                                        |
| <b>Stage Size (inches):</b><br>2.56 x 2.56                                                                        |
| <b>Straight Line Accuracy (µm):</b><br>10                                                                         |
| <b>Included Hardware:</b><br>4X 1/4"-20, 3/8"L Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |