

Dual Coarse/Fine Movement



#37-603

Stock **#37-603** 11 In Stock

-

1

+

A\$556⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$556.80 each
Qty 10+	A\$491.84 each
Need More?	Request Quote

Product Downloads

General

English	Type:
Not Lockable	Note:

Physical & Mechanical Properties

Linear (X)	Type of Movement:
	Guide System:

Dovetail	
20 x 100	Stage Size (mm):
40 (±20) Coarse, 2 (±1) Fine	Travel (mm):
3.5 Horizontal, 2.1 Vertical	Load Capacity (kg):
50	Straight Line Accuracy (µm):
15 Coarse, 0.11 Fine	Travel Per Knob Rotation (mm):
370	Weight (g):

Table Size (mm):	
20 x 57	

Hardware & Interface Connectivity

Type of Drive:	
Rack and Pinion	

Threading & Mounting

Mounting Threads:	
Stage: (1) ¼-20 Base: (2) 8-32	

Regulatory Compliance

RoHS 2015:	
Exempt	
Reach 224:	
Contains SVHC(s)	
Certificate of Conformance:	
View	

Product Details

- Multiple Configurations Available
- High Load Capacity
- Ideal for Applications Requiring Long Travel
- Additional [Rack and Pinion Stages](#) Available

Basic Rack and Pinion Stages are ideal for applications requiring high load capacity or long travel. These stages feature horizontal load capacities of 3.5kg and vertical load capacities of 2.1kg. Each stage offers stage and base mounting holes and features steel construction with brass movement. Basic Rack and Pinion Stages are available in multiple configurations with varying stage sizes. These stages have a Dovetail guide system.

Technical Information

