

TECHSPEC[®] Elliptical Mirror 38.1mm Minor Axis Uncoated



Stock #32-096 3-5 DAYS

-

1

+

A\$198.40

ADD TO CART

Qty 1-5

A\$198.40

Qty 6+

A\$158.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Minor Axis (mm):
38.10

Major Axis (mm):
53.87

Surface Flatness (P-V):
λ/8

Substrate:

[BOROFLOAT®](#)

Surface Quality:
60-40

Dimensional Tolerance (mm):
±0.38

Dimensional Tolerance (inches):
±0.015

Coating:
Uncoated

Coating Type:
Uncoated

Clear Aperture CA (mm):
34.29 (Minor Axis)
48.49 (Major Axis)

Note:
Flatness specification is Peak to Valley

Thickness (mm):
9.53

Thickness Tolerance (inches):
±0.030

Thickness Tolerance (mm):
±0.76

Type:
Flat Mirror

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 211:
[Compliant](#)

Certificate of Conformance:
[View](#)