

English Post Pivot Base



Stock **#53-355** 20+ In Stock

-

1

+

A\$36^{.80}

ADD TO CART

Volume Pricing	
Qty 1-9	A\$36.80 each
Qty 10+	A\$32.96 each
Need More?	Request Quote

Product Downloads

General	
English	Type:
Includes 1/4-20 Cap Screws	Note:
English Type (1/4-20)	Compatible Post Holder:

Physical & Mechanical Properties

47.80

Length (mm):

19.10	Width (mm):
9.50	Thickness (mm):
Black Anodized Aluminum	Construction:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Slot Adjustment Range of 1.00"
- The narrow slotted mounting base is used for the positioning of 0.5" dia. stainless steel posts and post holder assemblies. The post/post holder is attached to the base via a counterbored clearance hole with a 1/4-20 socket screw. The base is held in place with another socket screw in the slot. The slot length allows the post to be centered at the mid-point laterally or at 45° on a 1" center hole breadboard. Anodized aluminum.

Technical Information

