

[All Products](#) / [Cameras](#) / [Analog Cameras](#) / [EO Color CCD Cameras](#)

[See all 1 Products in Family](#)

# EO-3AN 1/3" CCD Color Analog Camera, NTSC



Stock #88-408 3-5 DAYS

- 1 + **A\$792.00**

ADD TO CART

Qty 1+

A\$792.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Video Output:**  
Analog

**Type:**  
Color Camera

**Mounting Threads:**  
1/4-20 (Integrated into Housing)

**Image Buffer:**  
Not Specified

|                                                                                |
|--------------------------------------------------------------------------------|
| <b>Model Number:</b><br>EO-3AN                                                 |
| <b>Type of Sensor:</b><br>Interlaced CCD                                       |
| <b>Camera Sensor Format:</b><br>1/3"                                           |
| <b>Resolution (MegaPixels):</b><br>0.40                                        |
| <b>Pixels (H x V):</b><br>976 x 494                                            |
| <b>Pixel Size, H x V (µm):</b><br>4.9 x 6.9                                    |
| <b>Sensing Area, H x V (mm):</b><br>4.8 x 3.4                                  |
| <b>Exposure Time:</b><br>Auto/Manual 1/60-1/100,000s                           |
| <b>Connector:</b><br>Analog, BNC, Y-C                                          |
| <b>Power Supply:</b><br>Separate Power Supply (Included)                       |
| <b>Power Consumption (W):</b><br>2.5                                           |
| <b>GPIOs:</b><br>N/A                                                           |
| <b>Synchronization:</b><br>Internal                                            |
| <b>Dimensions (mm):</b><br>51.6 x 41 x 41 (includes connectors and lens mount) |
| <b>Weight (g):</b><br>140                                                      |
| <b>Mount:</b><br>C/CS-Mount                                                    |
| <b>Housing:</b><br>Full                                                        |
| <b>Interface Port Orientation:</b><br>Back Panel                               |
| <b>Dynamic Range (dB):</b><br>Not Specified                                    |
| <b>Operating Temperature (°C):</b><br>-10 to +50                               |
| <b>GPIO Connector Type:</b><br>None                                            |
| <b>Power Requirement:</b><br>12 VDC                                            |
| <b>Signal Format:</b><br>NTSC                                                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |