

TECHSPEC[®] 30mm ID Kinematic Cage Mounting Plate



#85-663

Stock **#85-663** 1 In Stock

-

1

+

A\$288⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$288.00 each
Need More?	Request Quote

Product Downloads

General

Tip-Tilt

Function:

Circular/Cylindrical Tube

Type of Optics:

Physical & Mechanical Properties

30.0

Plate Inner Diameter (mm):

38.0

Bolt Circle Diameter for 6mm Dia. Thru (mm):

50.0	Outer Diameter (mm):
Black Anodized Aluminum	Construction:
50 Dia.	Dimensions (mm):
32.00	Thickness (mm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Specialized Plates Designed to Hold and Position Optics
 - Anodized Aluminum Construction with Stainless Steel Screws
 - X-Y Micro Positioning Plate with RMS Mounting Thread
- TECHSPEC® Cage System Adjustable Plates are used to integrate optical components into the TECHSPEC Cage System while providing rotary, tip-tilt, or linear adjustment. Rotary Mounts are available with M6 or 1/4-20 mounting threads and are designed to fit within the inner diameter of 25mm [cage system plates](#). The Kinematic Cage Mounting Plate is compatible with 30mm [cage system plates](#) and enables kinematic adjustment of cage system assemblies. The X-Y Micro Position Stage Plate also has 6mm rod holes, and features a 7mm clear aperture, X-Y micro-positioner, and an RMS threaded mount for precision mounting alignment.