

1/4" x 24", Flexible Fiber Optic Light Guide



1/4" Flexible Fiber Optic Light Guide

Stock #42-346 3-5 DAYS

- 1 + **A\$240.00**

ADD TO CART

Qty 1+
A\$240.00
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Acceptance Angle (°): 68.00
Minimum Bend Radius (mm): 38.1
Diameter (inches): 0.25
Length (inches): 24.00

Numerical Aperture NA: 0.55
Operating Temperature (°C): -40 to +107
Fiber Diameter (µm): 50.00
Packing Fraction (%): 82% nominal
Index of Refraction n_d - Core: 1.581
Index of Refraction n_d - Cladding: 1.487
Type of Illumination: Fiber Optic Light Guide
Compatible Light Guide Adapter: SX: #38-944 MX: #66-905
Geometry: Spot Light

Regulatory Compliance

Reach 174: Compliant
RoHS: Compliant
Certificate of Conformance: View
