

3/4" Dia Stainless Posts, Vertical Post 24"



Stock #52-100 **8 In Stock**

⊖ 1 ⊕ A\$202⁷⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$202.70 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Mounting Post **Type:**

Physical & Mechanical Properties

609.6 **Length (mm):**

2.25	Weight (lbs):
24.0	Length (inches):
3/4	Diameter (inches):

Threading & Mounting

3/4-16 Male (One End)	Mounting Threads:
-----------------------	--------------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Posts for Integration into Imaging Systems
- Vertical Posts Thread to Bases and Platforms
- Horizontal Arms Thread to Posts and Microscope Head Mounts
- [Rack and Pinion Focusing Mounts](#), and [Accessories](#) also Available

Stainless Steel Posts for Imaging Systems are used for constructing and supporting imaging systems. Vertical posts can be threaded directly into bases or platforms and include a steel collar with a set screw. Horizontal arms can be used with a 90° angle mount, on vertical posts, or with a breadboard adapter. Stainless Steel Posts for Imaging Systems are 3/4 of an inch in diameter and are offered in lengths ranging from 9.0 inches (228.6mm) to 24.0 inches (609.6mm). The mounting threads for these posts are available threaded on one end with 3/4"-16 male or threaded on both ends with a combination of 1/4"-20 and 5/16"-18 pins.