

Hoya G530 (VIS) 50.8mm Square, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-438** 3-5 DAYS

-

1

+

A\$172.80

ADD TO CART

Qty 1-10

A\$172.80

Qty 11+

A\$155.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.8 x 50.8

Center Wavelength CWL (nm):
530.00

Density (g/cm³): 3.12
Full Width-Half Max FWHM (nm): 50.00
Glass/Filter Number: Hoya G530
Substrate: ☐ Colored Glass
Length (mm): 50.80
Coating: Uncoated
Color: Green
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 50.80
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View