



Hoya G533 (VIS) 25.4mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-449** [CONTACT US](#)

- 1 + **A\$102.40**

ADD TO CART

Qty 1-10
A\$102.40
Qty 11+
A\$91.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40

Center Wavelength CWL (nm):
533.00

Density (g/cm³): 2.60
Full Width-Half Max FWHM (nm): 95.00
Glass/Filter Number: Hoya G533
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Green
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: VIS
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View