

Hoya G550 (VIS) 25.4mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-453** 3-5 DAYS

- 1 +

A\$102.40

ADD TO CART

Qty 1-10

A\$102.40

Qty 11+

A\$91.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40

Center Wavelength CWL (nm):
550.00

Density (g/cm³): 2.58
Full Width-Half Max FWHM (nm): 180.00
Glass/Filter Number: Hoya G550
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Green
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: VIS
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View