

GigE, patch cable Cat6, dragchain, screwable, 5m

See More by [IDS Imaging Development Systems](#)



GigE, patch cable Cat6, dragchain, screwable, 5m

Stock **#28-733** 1 In Stock

-

1

+

A\$238^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	A\$238.40 each
Need More?	Request Quote

Product Downloads

General	
CK00120	Model Number:
IDS Imaging Development Systems	Manufacturer:
Hardware & Interface Connectivity	
5	Length of Cable (m):
RJ45, screwable, to RJ45	Connector:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- 10GBASE-T (10GigE) Ethernet Interface, 10X Faster than GigE
- Up to 12.3MP Resolution with Framerrates up to 98fps
- Compatible with 1GigE, 2.5GigE and 5GigE Interfaces

IDS Imaging uEye Warp10 10GigE Cameras are capable of providing high quality, reliable image transfers at cable lengths of up to 100m on CAT6A or 40m on CAT5e. These global shutter cameras offer up to 12.3MP resolution. The 10GigE Ethernet interface provides up to 10X faster speeds than GigE for framerates up to 98fps for applications requiring high bandwidth. IDS Imaging uEye Warp10 10GigE Cameras are backwards compatible with existing 1GigE, 2.5GigE or 5GigE interfaces and will adjust their speed automatically. These cameras are ideal for machine vision, metrology, electronics inspection, and sports/motion analysis applications. These GeniCam compliant cameras are designed for the [IDS Peak software](#) but are compatible with most other GeniCam software protocols.