

Glan-Laser Polarizer 350 - 2300nm, 8mm



Glan-Laser Polarizer

Stock **#89-551** [CONTACT US](#)

⊖ 1 ⊕

A\$1,440.00

ADD TO CART

Qty 1-5
A\$1,440.00
Qty 6+
A\$1,368.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 8.0
Coating: Single Layer MgF ₂
Diameter (mm): 25.40
Extinction Ratio:

<5 x 10 ⁻⁵
Substrate: Calcite
Length (mm): 24.50
Surface Quality: 20-10
Type: Linear Polarizer
Construction: Crystalline Glan-Laser Polarizer
Transmitted Wavefront, P-V: λ/2 @ 632.8nm
Beam Deviation (arcmin): <3
Transmitted Wavefront Distortion (RMS): λ/4 @ 632.8 nm
Wavelength Range (nm): 350 - 2300
Damage Threshold, By Design: 5 J/cm² @ 1064nm, 10ns, 10Hz

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant