


Green Fluorescent Filter (G9), 50mm Square



Stock **#84-887** 3-5 DAYS

- 1 + **A\$1,104.00**

ADD TO CART

Qty 1-9
A\$1,104.00
Qty 10+
A\$971.20
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm): 50.0 x 50.0 ±0.10
Glass/Filter Number: G9
Substrate: ☐ Lumilass

Length (mm): 50.00
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.694
Transformation Temperature (°C): 660.00
Thickness (mm): 3.00 ±0.10
Type: Color Filter
Width (mm): 50.00
Peak Emission Wavelength (nm): 540.00
Excitation Wavelength (nm): 200 - 390
Peak Excitation Wavelength (nm): 365.00
Minimum Sensitivity: ~1μW/cm ²

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant