

Green M39 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-420** 3-5 DAYS



1



A\$272.00

ADD TO CART

Qty 1-9

A\$272.00

Qty 10+

A\$259.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-470, 600-951

Clear Aperture CA (mm):

34.00

Coating:

Hard Coated

Filter Thread:

M39 x 0.50
Color: Green
Center Wavelength CWL (nm): 525.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 80.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 41.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View