

TECHSPEC[®] Green M62.0 x 0.75 High Performance Machine Vision Filter



TECHSPEC[®] High Performance Mounted Machine Vision Filters

Stock #89-792 3-5 DAYS

- 1 +

A\$624.00

ADD TO CART

Qty 1-9

A\$624.00

Qty 10+

A\$575.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-450, 600-1000

Clear Aperture CA (mm):

57.5

Coating:

Hard Coated

Filter Thread:

M62.0 x 0.75
Color: Green
Center Wavelength CWL (nm): 525.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 92.00
Mount Thickness (mm): 5.5
Mount Thickness Including Threads (mm): 8.0
Note: OD ≥3.0 @ 600 - 1000nm OD ≥4.0 @ 200 - 450nm
Optical Density OD (Average): ≥3.0
Outer Diameter (mm): 65.0
Substrate Thickness (mm): 1.75 ±0.10
Type: Mounted Imaging Filter
Average Transmission (%): ≥90
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View