

## Hemisphere Foot (Package of 4), Sorbothane Bumpers



Hemisphere Foot (Package of 4), Sorbothane Bumpers, #35-264

Stock **#35-264** **1 In Stock**

A\$53<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-2	A\$53.20 each
Qty 3+	A\$47.52 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Universal **Type:**

### Physical & Mechanical Properties

1.0 **Thickness (inches):**

Sorbothane **Construction:**

**Diameter (inches):**

2.00

25-38 per bumper

**Load Capacity (lbs):**

---

## Regulatory Compliance

[Compliant](#)

**RoHS 2015:**

[View](#)

**Certificate of Conformance:**

---

## Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.

---

;