

High Gain, Premier Laser Diode Detector



Premier Laser Diode Detector

Stock **#58-764** 3-5 DAYS

− 1 +

A\$342.40

ADD TO CART

Qty 1+

A\$342.40

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

AC & DC S/N Ratio for 1mW Input (dB):
>60

AC Output Frequency Response (kHz):
>100

AC Output Sensitivity @ 650nm (V/mW):
10.00

Connector:
4 pin JST

Current (mA): 1.00
Diameter (mm): 15.00
Length (mm): 51.00
Operating Temperature (°C): -10 to +70
Relative Ambient Light Rejection (dB): 10.00
Type: High Gain
Voltage (V): 5 - 10 DC
Weight (g): 50.00
Construction: Black Anodized Aluminum
Power Supply: Power Supply Required and Sold Separately. USA: #59-099 Europe: Not Available Japan: #59-099 Korea: Not Available China: #59-099
Operating Humidity: 90% RH
Storage Temperature (°C): -40 to +85
Electrical Leads/ Pin Connections: 4 input/output leads

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View