

High Resolution Microscopy Star Target



High Resolution Mcroscopy Star Target, #37-538

Stock **#37-538** [CONTACT US](#)

⊖ 1 ⊕

A\$2,486.40

ADD TO CART

Qty 1-4
A\$2,486.40
Qty 5+
A\$2,362.40
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
10 x 10 x 1

Substrate: [Fused Silica](#) w/Chrome deposit

Optical Density OD (Average):
OD>7 @ 400nm, 6 @ 550nm, 4.5 @ 750nm, 3.6 @ 1000nm

Construction: Stainless Steel, 75 x 25 x 1.5mm, microscope slide format
Pattern: 1 central Siemens star with 36 segment pairs, 8mm diameter
Spectral Range: 200 - 2000nm
Pattern Tolerance: 100nm/cm = 10 ⁻⁵

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View