

Hoya B390 (UV-VIS) 12mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-781** 3-5 DAYS

[Additional Bandwidths](#)

− 1 +

A\$59.20

ADD TO CART

Qty 1-10	
A\$59.20	
Qty 11+	
A\$52.80	
Volume Pricing	
Request Quote	

Get Product Downloads



Diameter (mm):
12.00

Center Wavelength CWL (nm):

390.00
Density (g/cm³): 2.57
Full Width-Half Max FWHM (nm): 125.00
Glass/Filter Number: Hoya B390
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Blue-Violet
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View