

# Hoya IR85N (850nm), 25.4mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-905 3-5 DAYS

⊖ 1 ⊕

A\$70.40

ADD TO CART

Qty 1-10

A\$70.40

Qty 11+

A\$62.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
25.40

Cut-On Wavelength (nm):  
850.00 ±10

Density (g/cm³):  
490

|                                                             |
|-------------------------------------------------------------|
| <b>Glass/Filter Number:</b><br><a href="#">Hoya IR85N</a>   |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Color:</b><br>Black                                      |
| <b>Surface Quality:</b><br>60-40                            |
| <b>Transformation Temperature (°C):</b><br>3.02             |
| <b>Thickness (mm):</b><br>1.00                              |
| <b>Thickness Tolerance (mm):</b><br>±0.1                    |
| <b>Type:</b><br>Longpass Filter                             |
| <b>Wavelength:</b><br>IR                                    |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                  |
| <b>Reflection Factor P<sub>d</sub>:</b><br>0.91             |
| <b>Bevel:</b><br>Protective as needed                       |
| <b>Δλ (nm):</b><br><60                                      |
| <b>TH (%):</b><br>N/A                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |