

Hoya L42 (420nm), 25.4mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-850 3-5 DAYS



1



A\$70.40

ADD TO CART

Qty 1-10

A\$70.40

Qty 11+

A\$62.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40

Cut-On Wavelength (nm):
420.00 ±5

Density (g/cm³):
2.59

Glass/Filter Number: Hoya L42
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 60-40
Transformation Temperature (°C): 550
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View