

Hoya L42 (420nm), 50mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-851 3-5 DAYS

- 1 + **A\$140.80**

ADD TO CART

Qty 1-10
A\$140.80
Qty 11+
A\$124.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
420.00 ±5

Density (g/cm³):
2.59

Glass/Filter Number: Hoya L42
Substrate: Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 60-40
Transformation Temperature (°C): 550
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View