

# Hoya U330 (UV) 25.4mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-762** 3-5 DAYS

[Additional Bandwidths](#)

- 1 +

**A\$126.40**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$126.40                     |
| Qty 11+                       |
| A\$112.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.40

Center Wavelength CWL (nm):

|                                                      |
|------------------------------------------------------|
| 330.00                                               |
| Density (g/cm³):<br>2.78                             |
| Full Width-Half Max FWHM (nm):<br>140.00             |
| Glass/Filter Number:<br><a href="#">Hoya U330</a>    |
| Substrate: <input type="checkbox"/><br>Colored Glass |
| Coating:<br>Uncoated                                 |
| Color:<br>Black                                      |
| Surface Quality:<br>60-40                            |
| Thickness (mm):<br>1.00                              |
| Thickness Tolerance (mm):<br>±0.1                    |
| Type:<br>Bandpass Filter                             |
| Wavelength:<br>UV                                    |
| Parallelism (arcmin):<br>≤2                          |
| Dimensional Tolerance (mm):<br>±0.2                  |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |