

Hoya U360 (UV) 25.4mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-772** 3-5 DAYS

[Additional Bandwidths](#)

- 1 +

A\$126.40

ADD TO CART

Qty 1-10
A\$126.40
Qty 11+
A\$112.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40

Center Wavelength CWL (nm):

360.00
Density (g/cm³): 2.74
Full Width-Half Max FWHM (nm): 45.00
Glass/Filter Number: Hoya U360
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: UV
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
