

Hoya Y52 (520nm), 25.4mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-873 3-5 DAYS

- 1 +

A\$70.40

ADD TO CART

Qty 1-10

A\$70.40

Qty 11+

A\$62.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40

Cut-On Wavelength (nm):
520.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya Y52
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 60-40
Transformation Temperature (°C): 560
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View