

[See all 66 Products in Family](#)

IDS GV-5240FA-M-GL, GigE, 1/1.8" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock **#26-296** **1 In Stock**

-

1

+

A\$1,328⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,328.00 each
Need More?	Request Quote

Product Downloads

Monochrome		Spectrum:
General		
Monochrome Camera		Type:
GV-5240FA-M-GL		Model Number:
		Manufacturer:

IDS Imaging Development Systems	
uEye+ FA	Camera Series:
Physical & Mechanical Properties	
Dimensions (mm): 41 x 53 x 42.7 (excludes connectors and lens mount)	
Weight (g): 173	
Housing: Full	
Sensor	
Image Buffer: 128MB	
Sensor Format: 1/1.8"	
Resolution (Megapixels): 1.31	
Frame Rate (fps): 59.00	
Pixels (H x V): 1,280 x 1,024	
Pixel Size, H x V (µm): 5.30 x 5.30	
Sensing Area, H x V (mm): 6.784 x 5.427	
Imaging Sensor: e2v EV76C560	
Type of Sensor: Progressive Scan CMOS	
Shutter Type: Rolling / Global / Global Start	
Pixel Depth: 10 bit	
Exposure Time: 0.009ms - 169ms	
Dynamic Range (dB): 62.00	
Machine Vision Standard: GigE Vision	
Electrical	
Power Consumption (W): 1.7 - 2.2	
Hardware & Interface Connectivity	
Interface: GigE (PoE)	
Connector: GigE M12, screwable	
Power Supply: Power over Ethernet (PoE) or 12 - 24VDC via GPIO with #19-692	
GPIOs: 2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground	
Synchronization: Hardware Trigger (GPIO); Software Trigger	
Interface Port Orientation: Back Panel	
GPIO Connector Type: 8-pin Binder connector (Binder series 712: 09-0427-020-08)	
Threading & Mounting	
Mount: C-Mount	
Mounting Threads: ¼-20 with Tripod Mount Adapter #19-694	
Environmental & Durability Factors	
Operating Temperature (°C): 0 to +55	
Storage Temperature (°C): -20 to +60	

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.