

[See all 105 Products in Family](#)

## IDS U3-3180CP-M-GL, USB 3.0, 1" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, CP Model (Front)



Stock **#24-084** **2 In Stock**

- 1 + **A\$1,824<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | <b>A\$1,824.00</b> each       |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Camera **Type:**

U3-3180CP-M-GL **Model Number:**

**Manufacturer:**

uEye+ CP **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
29 x29 x29 (excludes connectors and lens mount)

**Weight (g):**  
50

**Housing:**  
Full

## Sensor

**Image Buffer:**  
128MB

**Sensor Format:**  
1"

**Resolution (Megapixels):**  
5.30

**Frame Rate (fps):**  
73.00

**Pixels (H x V):**  
2,592 x2,048

**Pixel Size, H x V (µm):**  
4.80 x4.80

**Sensing Area, H x V (mm):**  
12.441 x9.83

**Imaging Sensor:**  
ON Semi PYTHON 5000

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
10 bit

**Exposure Time:**  
0.17ms - 500ms

**Dynamic Range (dB):**  
Not Specified

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
1.6 - 4.3

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB 3.0 micro-B, screwable

**Power Supply:**  
Power over USB

**GPIOs:**  
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Output  
Supply Voltage, 1 Ground

**Synchronization:**  
Hardware Trigger (GPIO)

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
8-pin Hirose connector (HR25-7TR-8PA(73))

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
¼-20 with Tripod Mount Adapter [#16-017](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +60

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 251:**

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.